

ENERGY AND COMFORT



Model 8371

Features and Benefits

- Variable time constant modes minimize display variations when measuring fluctuating flows
- K factor function enables flexibility for measuring a variety of diffusers
- Variety of hood sizes lets you take readings from most diffusers, registers or grilles
- Back-lit display is easy to read in poor lighting conditions

Ventilation Test Instruments

AccuBALANCE® Air Capture Hood

Model 8371

TSI's AccuBALANCE® Air Capture Hoods measure air volume flowing through registers, diffusers and grilles. Weighing just seven and a half pounds, these air capture hoods are easy to carry, lift and use. Simply hold the AccuBALANCE up to a diffuser or grille and read direct supply or exhaust airflow on the large digital display.



TRUST. SCIENCE. INNOVATION.

Specifications

AccuBALANCE Model 8371 Air Capture Hoods

Flow Range

30 to 2,000 cfm (15 to 1,000 l/s, 50 to 3,500 m³/hr)

Accuracy

±5% reading and ±5 cfm (±2.4 l/s, ±8.5 m³/hr)

Operating Temperature

32 to 140°F (0 to 60°C)

Weight

7.5 lbs (3.4 kg)[†]

Power

4 C-size batteries (4 alkaline batteries provided)

Battery Life

40 hours continuous use

Carrying Case

26 in. × 26 in. × 7 in. (660 mm × 660 mm × 180 mm)

Hood Sizes Available

Standard	24 in. × 24 in. (610 mm × 610 mm)
Optional	24 in. × 48 in. (610 mm × 1,220 mm)
	12 in. × 48 in. (305 mm × 1,220 mm)
	12 in. × 60 in. (305 mm × 1,525 mm)
	36 in. × 36 in. (915 mm × 915 mm)

Model 8930 Printer Specifications

Printing Method Thermal serial head system

Printing Speed Approximately 0.8 lines/sec

External Dimensions

5.3 in. × 5.1 in. × 2.5 in.
(135 mm × 130 mm × 64 mm)

Printer Interface 8 bit serial RS-232-C, 1200 baud

	8371
Density correction	•
K-factor	•
Variable time constant	•
Field calibration adjustment	•
Printer output	•
Back-lit display	•
Certificate of Calibration	•

[†]Using 24 in. × 24 in. (610 mm × 610 mm) hood
Specifications are subject to change without notice.

TSI Incorporated - 500 Cardigan Road, Shoreview, MN 55126-3996 USA

USA	Tel: +1 800 874 2811	E-mail: info@tsi.com	Website: www.tsi.com
UK	Tel: +44 149 4 459200	E-mail: tsiuk@tsi.com	Website: www.tsiinc.co.uk
France	Tel: +33 491 95 21 90	E-mail: tsifrance@tsi.com	Website: www.tsiinc.fr
Germany	Tel: +49 241 523030	E-mail: tsigmbh@tsi.com	Website: www.tsiinc.de
Sweden	Tel: +46 8 595 13230	E-mail: tsiab@tsi.com	Website: www.tsi.se
India	Tel: +91 80 41132470	E-mail: tsi-india@tsi.com	
China	Tel: +86 10 8260 1595	E-mail: tsibeijing@tsi.com	



TRUST. SCIENCE. INNOVATION.

Contact your local TSI Distributor or visit our website www.tsi.com for more detailed specifications.